

# Child / Adult Ventilator miniVent – 3



### High functionality in a compact body

### Made in Japan

### Compact and safe design

Compact and lightweight type, can be installed anywhere

The power source is AC, and the internal / external battery has three power sources. Expand the area of Respiratory care in the medical field.

## Lung Ventilator **miniVent-3**

**CROSS MEDICAL SERVICE Co., Ltd.** 

#### **Function**

Function
Ventilation mode
SIMV, CPAP can be selected
Ventilation frequency
mechanical ventilation frequency is 2-60 times with the key /Can be adjusted up to the minute
Inspiration time
Can adjust the Inspiration time from key to 03-3.0 seconds
Tidal volume
Adjustable to 50-2,500ml with the ventilation volume setting dial
Trigger sensitivity
The sensitivity can be adjusted from -9 to +20 hPa with the key.
PEEP/CPAP
PEEP level in each mode can be adjusted to 0-+20 hPa
Lower airway pressure alarm
Out of the breathing circuit for the leak
The lower limit pressure can be adjusted to 5-40hPa with the key
Airway pressure maximum limit alarm
Finds breathing circuit blockages and tube blockages
High pressure alarm can be adjusted to the key 10-100hPa
Alarm indicator
When the alarm is activated the indicator of each item blinks to notify you.
Alarm sound temporary mute key (power failure alarm stop function)
Operate when you want to pause the alarm sound by suction operation or when using the internal

#### Main specifications

Breathing mode	CMV SIMV, CPAP
Ventilation frequency	2-60 times
Inspiration time	03–3.0 seconds
Tidal volume	50-2, 500ml
Maximum intake flow rate	Oxygen 100% setting=10-50 L / min Oxygen 45% setting = 10-45 L / min
Fraction of inspiratory oxygen (FIO2)	100% or 45 $\pm$ 10% switch
Inspiration pose	10%, OFF
Trigger sensitivity	-9 to +20 hPa
PEEP/CPAP	0-+20 hPa
Internal / external battery	Operating for 2 hours or more / external power supply DC12V
Airway pressure meter	-10 to + 100hPa, LED bar graph display
Nurse call output	Alarm signal output possible
Alarm safety mechanism	Lower airway pressure alarm/Airway pressure maximum limit alarm/Supply gas pressure drop alarm
	Apnea alarm/AC power cut alarm/Low battery alarm/AC power off alarm sound stop
	I: E Reverse rotation setting display/Watch dog timer
Overpressure safety valve	Medical gas spurce 0.4 $\pm$ 0.05MPa
Required power supply	AC100V 50 / 60Hz, 18VA
/ rated voltage	
Equipment classification	Protection type class I / internal power supply,
against electric shock	Degree of protection: BF type mounting part
Size / weight	Body size: 270 (W) x 127 (H) x 220 (D) mm
	(Excluding protrusions such as handles)
	Body weight: 4.7kg (including internal battery)
	Frame size: 440 (W) x 962 (H) x 500 (D) mm
	Frame weight: 11.5kg



#### Manufacturer Cross Medical Service Co.,Ltd.

4-2-8, Ryougoku, Sumida-ku, Tokyo 130-0026, Japan TEL: 03-3633-6333 / FAX: 03-3633-1333 / URL: http://www.cross-ms.co.jp